



## WE 26-230 MVT Quick with quick-locking nut, rotating main handle, deadman switch

- Metabo Marathon motor with patented dust protection for long service life
- Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety
- Deadman's switch for high user protection
- Rotating back handle and side handle can be mounted at 3 positions for optimum handle position also when cutting
- Metabo Quick for tool-free disc change by means of a quick-locking nut
- Tool-free adjustable guard; twist-proof
- Starting current limitation prevents the actuation of the lock on start-up
- Electronic overload protection and restart protection
- Metabo VibraTech (MVT): integrated damping system and side handle to reduce vibrations in order to protect the user's health
- Metabo safety switch prevents unintentional start
- Auto-stop carbon brushes to protect the motor
- LED signal indicates triggered restart protection or overheating

Order no.	606475260
EAN code	4007430268341
Disc-Ø	230 mm // 9 "
Rated input power	2600 W
Output power	1800 W
No-load speed	6600 rpm
Speed at rated load	4800 rpm
Torque	18 Nm / 160 in-lbs
Spindle thread	M 14
Handle circumference	144 mm / 5.669 "
Weight (without power cable)	6.3 kg / 13.9 lbs
Cable length	4 m / 13 ft

### Scope of delivery

Guard, Inner support flange, Quick-locking nut, Metabo VibraTech (MVT) side handle