



WE 2400 - 230

- Robust motor
- Starting current limitation prevents the actuation of the lock on start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Side handle can be mounted in three positions
- Metabo safety switch prevents unintentional start
- Auto-stop carbon brushes to protect the motor

Order no.	606484000
EAN code	4061792177376
Disc-Ø	230 mm // 9 1/16 "
Rated input power	2400 W
Output power	1540 W
No-load speed	6600 rpm
Speed at rated load	5000 rpm
Torque	14 Nm / 124 in-lbs
Spindle thread	M 14
Handle circumference	141 mm / 5.551 "
Weight (without power cable)	6 kg / 13.2 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, Nut with two holes, Side handle, Flat-pin spanner