



KS 216 M

- Compact crosscut and mitre saw of the mobile M-class - light, precise, user-friendly
- Precision Cut Line (PCL): precise shadow cutting line without re-adjustment thanks to cleverly positioned LED
- Turntable with fast, precise setting of common angles using stop points
- Saw blade inclination from -2 to 47°, therefore also suited for undercuts
- Robust die-cast aluminium design for the highest demands
- Effective dust extraction via integrated dust scoop
- Extendable table width extensions, also removable to put underneath extremely long work pieces
- Quick-action clamp for secure fixing of the work piece from the top or front
- All scales and operating elements are visible from the working position and can be operated intuitively
- Ergonomic handle areas for carrying with one or two hands

Order no. EAN code	610216000 4061792218178
Dimensions	477 x 463 x 490 mm // 18.8 x 18.2 x 19.3 "
Support surface	155 x 725 mm // 6.1 x 28.54 "
Maximum cutting width 90°/45°	120 / 80 mm // 4.687 / 3 1/8 "
Maximum cutting depth at 90°/45°	60 / 45 mm // 2 3/8 / 1 3/4 "
Cutting capacity 90°/90°	120 x 60 mm // 4 11/16 x 2 3/8 "
Cutting capacity 45°/45°	80 x 45 mm // 3.1625 x 1 3/4 "
Turntable setting left/right	47 / 47 °
Saw blade tilt left/right	47 / 2 °
Saw blade	216 x 30 mm // 8 1/2 x 1.181 "
Rated input power	1100 W
Rated input power S1 100%	1100 W
Rated input power S6 20%	1350 W
No-load speed	5000 rpm
Speed at rated load	3800 rpm
Cutting speed	57 m/s // 187 ft/min
Weight	8.7 kg / 19.18 lbs
Cable length	2 m / 7 ft

Scope of delivery

Saw blade "precision cut wood - classic", 216x30, Z40, 2 Table length extensions, Length Guide, Material clamp, Tool for saw blade change, Chip Collection Bag