



NFR 18 LTX 90 BL

- Powerful cordless nailer with pneumatic impact technology for nails up to 90 mm length
- Fast work progress thanks to fire sequence of two nails per second
- Maximum freedom of movement when driving in nails without compressed air hose or cable
- Economical, safe operation without gas cartridge and addition service effort
- Efficient Brushless motor for up to 550 shots per battery pack charge (LiHD 4.0 Ah)
- Selection possible between single shot mode and contact triggering for fast nailing in series
- Tool-free adjustment of the driving-in depth for precise working
- Blank shot protection protects from unnecessary wear and tear and increases the service life of the nailer
- Energy-saving safety shutdown after 30 minutes of inactivity
- Multi-position handle to protect the battery pack, as attachment point for tool safety equipment and to suspend the nailer
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	612090840
EAN code	4061792226791
Battery voltage	18 V
Nail speed	2 /s
Magazine capacity nails	47
Nail strips angle	30 - 34 °
Nail length	50 - 90 mm // 1 31/32 - 3 9/16 "
Nail diameter	2.9 - 3.3 mm // 0.114 - 0.13 "
Weight without battery pack	4.1 kg / 9 lbs
Weight with battery pack	4.7 kg / 10.4 lbs

Scope of delivery

Multi-position handle, Rubber protective shoe, Magazine for nail strips, Hexagonal wrench, metaBOX 340, without battery pack, without charger