



MT 18 LTX

- Oscillating cordless multi-tool with high performance comparable to that of a mains powered version
- Indispensable for interior development such as cutting, sanding and scraping of different materials
- Tool holder for maximum compatibility to OIS, Starlock and other accessories
- Metabo Quick tool change system for time-saving, convenient change of accessories
- Quick work progress thanks to large oscillation angle and VTC-Electronics to maintain constant speed even under load
- Slim design and non-slip soft-grip surface for optimised handling
- Extra bright LED lights for good visibility of the working area
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

| Order no. | 613021840 |
|----------------------------------------------|----------------------------------|
| EAN code | 4007430287700 |
| Battery voltage | 18 V |
| Orbital frequency with no load | 7000 - 18000 rpm |
| Oscillation angle left/right | 1.6 ° |
| Bit retainer | Compatible with OIS and Starlock |
| Base plate, dimensions from corner to corner | 93 mm / 3 5/8 " |
| Weight without battery pack | 1.4 kg / 3.1 lbs |
| Weight with battery pack | 1.8 kg / 4 lbs |

Scope of delivery

Plunge saw blade 32 mm HCS (wood), Triangular hook and loop sanding plate 93 mm, 5 Hook and loop sanding sheets 93 mm P 80, 5 Hook and loop sanding sheets 93 mm P 120, Suction Adapter, Multi-adapter, metaBOX 145 L, without battery pack, without charger