



MT 18 LTX

- Oscillating cordless multi-tool with high performance comparable to that of a mains powered version
- Indispensable for interior development such as cutting, sanding and scraping of different materials
- Tool holder for maximum compatibility to OIS, Starlock and other accessories
- Metabo Quick tool change system for time-saving, convenient change of accessories
- Quick work progress thanks to large oscillation angle and VTC-Electronics to maintain constant speed even under load
- Slim design and non-slip soft-grip surface for optimised handling
- Extra bright LED lights for good visibility of the working area
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	613021890
EAN code	4007430277558
Battery voltage	18 V
Orbital frequency with no load	7000 - 18000 rpm
Oscillation angle left/right	1.6 °
Bit retainer	Compatible with OIS and Starlock
Base plate, dimensions from corner to corner	93 mm / 3 5/8 "
Weight without battery pack	1.4 kg / 3.1 lbs
Weight with battery pack	1.8 kg / 4 lbs

Scope of delivery

Plunge saw blade 32 mm HCS (wood), Triangular hook and loop sanding plate 93 mm, 5 Hook and loop sanding sheets 93 mm P 80, 5 Hook and loop sanding sheets 93 mm P 120, Suction Adapter, Multi-adapter, without battery pack, without charger