



MT 18 LTX BL QSL

- Oscillating cordless multi-tool with high performance comparable to that of a mains powered version
- For intensive applications in interior development with custom-fit 3D holder StarlockPlus
- Indispensable for interior development such as cutting, sanding and scraping of different materials
- Metabo Quick tool change: quick and comfortable thanks to magnetic holder to pre-fix the accessory
- Unique Metabo brushless motor highest efficiency when working, also in continuous mode
- Extra bright LED lights for good visibility of the working area
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	613088840
EAN code	4061792183940
Battery voltage	18 V
Orbital frequency with no load	8000 - 20000 rpm
Oscillation angle left/right	1.6 °
Bit retainer	Starlock/ Starlock-Plus
Base plate, dimensions from corner to corner	93 mm / 3 5/8 "
Weight without battery pack	1.3 kg / 2.9 lbs
Weight with battery pack	1.7 kg / 3.7 lbs

Scope of delivery

Plunge saw blade 32 mm (wood+metal), metaBOX 145 L, without battery pack, without charger