



PowerMaxx MT 12

- Oscillating cordless multi-tool with high performance comparable to that of a mains powered version
- Indispensable for interior development such as cutting, sanding and scraping of different materials
- Tool holder for maximum compatibility to OIS, Starlock and other accessories
- Slim design and non-slip soft-grip surface for optimised handling
- Extra bright LED lights for good visibility of the working area

Order no.	613089840
EAN code	4061792227514

Battery voltage	12 V
Orbital frequency with no load	5000 - 18000 rpm
Oscillation angle left/right	1.6 °
Bit retainer	Compatible with OIS and Starlock
Base plate, dimensions from corner to corner	93 mm / 3625 "
Weight without battery pack	0.8 kg
Weight with battery pack	1 kg

Scope of delivery

Plunge saw blade 34 mm BiM (wood+metal), Triangular hook and loop sanding plate 93 mm, 5 Hook and loop sanding sheets 93 mm P 80, 5 Hook and loop sanding sheets 93 mm P 120, metaBOX 145, without battery pack, without charger