



RWE 1200

- Robust 30 litre stirrer for powerful mixing and stirring on the construction site
- Minor effort to guide the stirrer thanks to ergonomically favourable handle position
- Rubber corners at the housing for effective protection from damage, safe storage and non-slip leaning against a wall
- The side cable exit reduces the risk of a cable break
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Splash-water proof motor cover to protect against dirt, mud and splash water
- Vario (V)-Electronics for working at customised speeds to suit various application materials

Order no.	614048000
EAN code	4061792221550
Rated input power	1200 W
Output power	580 W
No-load speed	0 - 900 rpm
Gears	1
Maximum stirring paddle diameter	120 mm / 4 23/32 "
Max. recommended mixing amount	30 l
Bit retainer	Female thread M 14
Collar diameter	50 mm / 1 31/32 "
Weight (without power cable)	3.4 kg / 7.5 lbs
Cable length	4 m / 13 ft

Scope of delivery

Stirrer paddle RS-R2 (Ø 120 mm), Open-jawed spanner