



RWEV 1600-2

- Powerful 1600 Watt stirrer with two speeds for demanding mixing applications up to 90 litres
- Minor effort to guide the stirrer thanks to ergonomically favourable handle position
- Rubber corners at the housing for effective protection from damage, safe storage and non-slip leaning against a wall
- The side cable exit reduces the risk of a cable break
- High torque thanks to two-speed gear for viscous materials
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Continuous speed control trigger with rubber cover to protect against dust and dirt deposits
- Splash-water proof motor cover to protect against dirt, mud and splash water
- Electronic soft start for splash-free working
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for work with materials requiring customised speeds, which remain constant under load
- Thumbwheel for speed preselection

Order no.	61405000
EAN code	4061792221536
Rated input power	1600 W
No-load speed	0 - 300 / 0 - 650 rpm
Gears	2
Maximum stirring paddle diameter	160 mm / 6 5/16 "
Max. recommended mixing amount	90 l
Bit retainer	Female thread M 14
Collar diameter	50 mm / 1 31/32 "
Weight (without power cable)	4.5 kg / 9.9 lbs
Cable length	4 m / 13 ft

Scope of delivery

Stirrer paddle RS-R3 (Ø 160 mm), Open-jawed spanner