



PE 15-20 RT

- Powerful polisher for fine grinding and high-gloss polishing of painted surfaces
- Maximum productivity thanks to powerful 1,500 Watt motor and high-performance planetary gear train
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Speed control trigger with locking function for controlled start-up until the preselected speed
- Optimal guidance thanks to rubberised front cap and slim handle area for low-fatigue working
- Overload protection: protects the motor from overheating
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Auto-stop carbon brushes to protect the motor

Order no.	61520000
EAN code	4007430323026
For backing pad up to maximum	180 mm / 7 "
Rated input power	1500 W
Output power	1000 W
No-load speed	300 - 1900 rpm
Speed at rated load	1720 rpm
Torque	18 Nm / 160 in-lbs
Spindle thread	M 14
Weight (without power cable)	2.4 kg / 5.3 lbs
Cable length	4 m / 13 ft

Scope of delivery

Side handle, (delivered without backing pad and polishing pad)