



## BAS 261 Precision

- High precision and stability for highest cutting quality
- Quiet belt path thanks to balanced flywheels with rubber coating
- Top and bottom HSS precision three-roller guide of the band saw blade for accurate cutting results, adjustable without tools
- Precise rip fence with double clamping and quick fastening
- Quiet induction motor, maintenance-free and robust.
- Restart protection: prevents unintentional start-up after power supply interruption
- Swivelling grey cast iron saw table for inclined cuts
- Door opening without tools for easy saw blade change
- Tool-less height adjustment of the saw blade guard
- LED work light for illumination of the cutting line
- External extraction possible for low-dust working
- Radius cutting with circle sawing attachment (accessory)

Order no.	619008000
EAN code	4007430304865
Dimensions	530 x 470 x 840 mm // 20 7/8 x 18 1/2 x 33 1/16 "
Support surface	328 x 335 mm // 12 29/32 x 13 3/16 "
Working height without stand	375 mm / 14 3/4 "
Sawing bench swivel range	0 - 45 °
Cutting height	103 mm / 4 1/16 "
Passage width	245 mm / 9 21/32 "
Cutting speed	735 m/min
Saw belt length	1712 mm / 67 13/32 "
Mains voltage	220 - 240 V
Rated input power	400 W
Output power	270 W
Weight	32.5 kg / 71.7 lbs

### Scope of delivery

Universal band saw blade A6, Rip fence, Mitre Fence, Suction adapter (for Ø 44, 58, 100 mm), Push stick