



Combo Set WE 2200-230 + W 750-125 with 2 diamond cutting discs

- W 750-125: robust, universal and economical: ergonomic angle grinder for any application, robust motor, twist-proof guard, restart protection after power interruption,
- WE 2200-230: Robust motor, starting current limitation with soft start prevents the actuation of the lock on start-up, side handle can be mounted in three positions, Metabo safety switch prevents unintentional startup


Order no.
EAN code

685172510
4061792171015


Scope of delivery

WE 2200-230, W 750-125, plastic carry case, diamond cutting disc SP 230x22.23 mm, diamond cutting disc SP 125x22.23 mm


Angle Grinder WE 2200-230

	Disc-Ø	230 mm // 9 "
	Rated input power	2200 W
	Output power	1520 W
	No-load speed	6600 rpm
	Speed at rated load	4300 rpm
	Torque	13.5 Nm / 120 in-lbs
	Spindle thread	M 14
	Handle circumference	142 mm / 5.591 "
	Weight (without power cable)	5.2 kg / 11.5 lbs
	Cable length	4 m / 13 ft
<ul style="list-style-type: none"> • Robust motor • Starting current limitation prevents the actuation of the lock on start-up • Restart protection: prevents unintentional start-up after power supply interruption • Side handle can be mounted in three positions • Metabo safety switch prevents unintentional start 		

Angle Grinder WE 2200-230

	Disc-Ø	230 mm // 9 "
	Rated input power	2200 W
	Output power	1520 W
	No-load speed	6600 rpm
	Speed at rated load	4300 rpm
	Torque	13.5 Nm / 120 in-lbs
	Spindle thread	M 14
	Handle circumference	142 mm / 5.591 "
	Weight (without power cable)	5.2 kg / 11.5 lbs
	Cable length	4 m / 13 ft
<ul style="list-style-type: none"> • Robust motor • Starting current limitation prevents the actuation of the lock on start-up • Restart protection: prevents unintentional start-up after power supply interruption • Side handle can be mounted in three positions • Metabo safety switch prevents unintentional start 		

Angle Grinder W 750-125

	Disc-Ø	125 mm // 5 "
	Rated input power	750 W
	Output power	475 W
	No-load speed	11500 rpm
	Speed at rated load	7000 rpm
	Torque	1.9 Nm / 16.8 in-lbs
	Spindle thread	M 14
	Handle circumference	180 mm / 7.094 "
	Weight (without power cable)	1.8 kg / 4 lbs
	Cable length	2.5 m / 8.2 ft
<ul style="list-style-type: none"> • Robust, universal and economical: ergonomic angle grinder for any application • Robust motor • Twist-proof guard • Restart protection after power interruption 		

Angle grinder W 750-125 Set



Disc-Ø	125 mm // 5 "
Rated input power	750 W
Output power	475 W
No-load speed	11500 rpm
Speed at rated load	7000 rpm
Torque	1.9 Nm / 16.8 in-lbs
Spindle thread	M 14
Handle circumference	180 mm / 7.094 "
Weight (without power cable)	1.8 kg / 4 lbs
Cable length	2.5 m / 8.2 ft
	<ul style="list-style-type: none"> • Robust, universal and economical: ergonomic angle grinder for any application • Robust motor • Twist-proof guard • Restart protection after power interruption