



Combo Set 3.1 SB 18 LT BL + W 18 L 9-125 Quick + KH 18 LTX 24

- Cordless hammer drill SB 18 LT BL: brushless cordless impact drill with optimal power for the demanding applications.
- Cordless angle grinder W 18 9-125 Quick: Robust angle grinder with powerful motor and slim design for universal applications.
- Cordless combination hammer KHA 18 LTX 24: Combination hammer with 3 functions: hammer drilling, drilling and chiseling

Order no.
EAN code

685212000
4061792224650

Scope of delivery

Cordless hammer drill SB 18 LT, cordless angle grinder W 18 LT 9-125 Quick, cordless combination hammer KH 18 LTX 24, 3 LiPOWER battery packs (18 V/5.2 Ah), charger ASC 55, tool bag (large)

Cordless hammer drill SB 18 LT BL



Battery voltage	18 V
Maximum torque, soft	34 Nm / 301 in-lbs
Maximum torque, hard	75 Nm / 663.8 in-lbs
Adjustable torque	0.7 - 8 Nm // 6 - 71 in-lbs
Drill-Ø masonry	13 mm / 1/2 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	38 mm / 1 1/2 "
No-load speed	0 - 600 / 0 - 2100 rpm
Maximum impact rate	31950 bpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.2 kg / 2.6 lbs
Weight with battery pack	1.6 kg / 3.5 lbs
• A powerful all-around choice: easy to handle hammer drill with brushless power for challenging drilling and screw fitting applications • Powerful Brushless motor for greatest efficiency and long battery pack runtime • High-performance impact mechanism for optimum drilling performance • Overload protection: protects the motor from overheating • Integrated working light to illuminate the contact area • Integrated LED work light with afterglow function for optimal brightness in the work area • With handy belt hook and bit case which can be fixed either on the right or left side • Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com	

Cordless angle grinder W 18 L 9-125 Quick



Battery voltage	18 V
Disc-Ø	125 mm / 5 "
Max. cutting depth	34 / 1.339 "
No-load speed	8500 rpm
Spindle thread	M 14
Handle circumference	191 mm / 7.52 "
Weight without battery pack	1.6 kg
Weight with battery pack	2.3 kg
• Robust angle grinder with powerful motor and slim design for universal applications • Metabo Quick for tool-free disc change by means of a quick-locking nut • Tool-free adjustable guard; twist-proof • Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety • Electronic soft start for smooth start-up • Restart protection: prevents unintentional start-up after battery pack change • Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com	

Cordless combination hammer KH 18 LTX 24



Battery voltage	18 V
Max. single blow energy (EPTA)	2.1 J
Maximum impact rate	5200 bpm
Drill-Ø concrete with hammer drills	24 mm / 1 "
Drill-Ø masonry with core bits	68 mm / 2 11/16 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	30 mm / 1 3/16 "
No-load speed	0 - 1400 rpm
Bit retainer	SDS-plus
Weight without battery pack	2.6 kg / 5.73 lbs
• Cordless hammer with SDS plus holder for powerful hammer drilling and chiselling - any time and anywhere • Combination hammer with 3 functions: hammer drilling, drilling and chiselling • Variospeed (V) Electronics for working at customised speeds to suit various application materials • Electronic soft start for precise spot-drilling • Safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly • With attachment point for tool safety straps for working at great heights • LED work light for optimum view of the drilling site • Dust-free drilling with external dust extraction ESA plus (accessory) • Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com	