



Drill stand 890

- The design of the feed mechanism enables the maximum drilling depth of 65 mm to be achieved with a swivelling motion
- Asymmetrical arrangement of the column in relation to the base plate enables the processing of larger workpieces
- Unlimited access to the controls of drill and drill stand by angled cantilever
- No risk of injury or drill breakage thanks to the safe adjustment of the device carrier to the required working height
- Adjustable depth guide

Order no.	600890000
EAN code	4007430143396
Distance, bit centre to column	165 mm / 6 1/2 "
Working stroke	65 mm / 2 9/16 "
Height of column	500 mm / 20 "
Column Ø	40 mm / 1 9/16 "
Aperture	43 mm
Base plate	220 x 213 mm // 8 21/32 x 8 3/8 "
Weight	5.5 kg / 12.13 lbs