



Flexiamant super 125x2.0x22.23 steel, cutting disc, offset type

- Universal disc for complete metal processing
- Hardness: hard
- Extremely high cutting output with good tool life by using special corundums
- Best results using powerful angle grinders
- Maximum working speed 80 m/s

Order no.	616101000
EAN code	4007430437341
Quality class	A 36-T
Diameter x thickness x bore	125 x 2 x 22.23 mm
Version	offset
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25