



## Flexiamant super 180x2.0x22.23 steel, cutting disc, offset type

- Universal disc for complete metal processing
- Hardness: hard
- Extremely high cutting output with good tool life by using special corundums
- Best results using powerful angle grinders
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>616102000</b>
<b>EAN code</b>	<b>4007430437358</b>
Quality class	A 36-T
Diameter x thickness x bore	180 x 2 x 22.23 mm
Version	offset
Maximum speed	8500 rpm
Sales unit / packaging unit	1 / 25