



Flexiamant super 230x2.5x22.23 steel, cutting disc, straight type

- Universal disc for complete metal processing
- Hardness: hard
- Extremely high cutting output with good tool life by using special corundums
- Best results using powerful angle grinders
- Maximum working speed 80 m/s

Order no.	61611500
EAN code	4007430400093
Quality class	A 36-T
Diameter x thickness x bore	230 x 2,5 x 22,23 mm
Version	straight
Maximum speed	6600 rpm
Sales unit / packaging unit	1 / 25