



Flexiamant 230x3.0x22.23 steel, cutting disc, straight type

- Universal disc for complete metal processing
- Hardness: medium
- High cutting output with long tool life
- Uniform in cutting output and tool life
- Maximum working speed 80 m/s

Order no.	616127000
EAN code	4007430400246
Quality class	A 30-R
Diameter x thickness x bore	230 x 3 x 22.23 mm
Version	straight
Maximum speed	6600 rpm
Sales unit / packaging unit	1 / 25