



## Flexiarapid 150x1.6x16.0 Inox, cutting disc, straight type

- Thin high-output cutting disc especially for stainless, thin-walled materials such as pipes, metal sheets, profiles, wires
- Hardness: hard
- Very high cutting output with good tool life by using special corundums
- Low material consumption, power-saving, low machine load.
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- Maximum working speed 80 m/s
- A 60-R with 1 mm thickness; A 46-R with 1.6 mm thickness; A 30-R with 1.9 mm thickness

<b>Order no.</b>	<b>61618000</b>
<b>EAN code</b>	<b>4007430441652</b>
Quality class	A 46-R
Diameter x thickness x bore	105 x 1.6 x 16 mm
Version	straight
Maximum speed	15300 rpm
Sales unit / packaging unit	1 / 25