



## Flexiarapid 230x1.9x22.23 Inox, cutting disc, straight type

- Thin high-output cutting disc especially for stainless, thin-walled materials such as pipes, metal sheets, profiles, wires
- Hardness: hard
- Very high cutting output with good tool life by using special corundums
- Low material consumption, power-saving, low machine load.
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- Maximum working speed 80 m/s
- A 60-R with 1 mm thickness; A 46-R with 1.6 mm thickness; A 30-R with 1.9 mm thickness

Order no.	61618500
EAN code	4007430441706
Quality class	A 30-R
Diameter x thickness x bore	230 x 1.9 x 22.23 mm
Version	straight
Maximum speed	6600 rpm
Sales unit / packaging unit	1 / 25