



Flexiarapid super 125x1.6x22.23 Inox, cutting disc, straight type

- The super-thin high-output disc especially for processing stainless steel
- Super quick with very long service life thanks to the use of special corundums
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- For all rust and acid resistant steels (V2A, Nirosta, INOX), spring steels, tool steels
- For use in the manufacture of vehicles, containers, car bodies, switch cabinets etc.
- Cutting discs for quiet, precise cutting, cuts without burrs
- Hardness: hard
- Maximum working speed 80 m/s

| Order no. | 61622000 |
|-----------------------------|----------------------|
| EAN code | 4007430135391 |
| Quality class | A 46-U |
| Diameter x thickness x bore | 125 x 1.6 x 22.23 mm |
| Version | straight |
| Maximum speed | 12200 rpm |
| Sales unit / packaging unit | 1 / 25 |