



Flexiarapid super 180x1.6x22.23 Inox, cutting disc, offset type

- The super-thin high-output disc especially for processing stainless steel
- Super quick with very long service life thanks to the use of special corundums
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- For all rust and acid resistant steels (V2A, Nirosta, INOX), spring steels, tool steels
- For use in the manufacture of vehicles, containers, car bodies, switch cabinets etc.
- Cutting discs for quiet, precise cutting, cuts without burrs
- Hardness: hard
- Maximum working speed 80 m/s

Order no.	616227000
EAN code	4007430135087
Quality class	A 36-U
Diameter x thickness x bore	180 x 1.6 x 22.23 mm
Version	offset
Maximum speed	8500 rpm
Sales unit / packaging unit	1 / 25