



## Flexiarapid super 230x1.9x22.3 Inox, cutting disc, offset type

- The super-thin high-output disc especially for processing stainless steel
- Super quick with very long service life thanks to the use of special corundums
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- For all rust and acid resistant steels (V2A, Nirosta, INOX), spring steels, tool steels
- For use in the manufacture of vehicles, containers, car bodies, switch cabinets etc.
- Cutting discs for quiet, precise cutting, cuts without burrs
- Hardness: hard
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>616229000</b>
<b>EAN code</b>	<b>4007430135063</b>

Quality class	A 36-U
Diameter x thickness x bore	230 x 1.9 x 22.23 mm
Version	offset
Maximum speed	6600 rpm
Sales unit / packaging unit	1 / 25