



Flexiamant super 115x6.0x22.23 steel, grinding disc, offset type

- Universal disc for all metal processing requirements
- Especially suitable for deburring and grinding edges, also for cast processing
- Hardness: hard
- Good cutting output with extremely good tool life
- Maximum working speed 80 m/s

| | |
|-----------------------------|----------------------|
| Order no. | 616275000 |
| EAN code | 4007430061096 |
| Quality class | A 24-T |
| Diameter x thickness x bore | 115 x 6 x 22.23 mm |
| Version | offset |
| Maximum speed | 13300 rpm |
| Sales unit / packaging unit | 1 / 25 |