



M-Calibur 125 x 1.6 x 22.23 Inox, TF 41

- The latest generation of cutting discs with ceramic abrasive grain
- Maximum cutting performance with extremely high tool life thanks to using ceramic special corundum and new bonding
- Highest productivity and work progress
- Low in iron, sulphur and chlorine ($\text{Fe} + \text{S} + \text{Cl} \leq 0.1\%$)
- For all rust and acid resistant steels (V2A, Nirosta, INOX), high-alloy steels, spring steels, tool steels
- Hardness: hard
- Maximum working speed 80 m/s

Order no. EAN code	61628600 4007430256805
Quality class	CA 46-U
Diameter x thickness x bore	125 x 1.6 x 22.23 mm
Version	straight
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25