



M-Calibur 125 x 7.0 x 22.23 Inox, SF 27

- The latest generation of grinding discs with ceramic grinding media
- Maximum material removal with extremely high tool life thanks to special ceramic corundum with new bonding
- Highest productivity and work progress
- Low in iron, sulphur and chlorine ($\text{Fe} + \text{S} + \text{Cl} \leq 0.1\%$)
- For all rust and acid resistant steels (V2A, Nirosta, INOX), high-alloy steels, spring steels, tool steels
- Maximum working speed: 80 m/s
- Hardness: medium-hard

Order no.	616291000
EAN code	4007430256829
Quality class	CA 36-O
Diameter x thickness x bore	125 x 7 x 22.23 mm
Version	offset
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25