



## Flexiamant 230x3.0x22.23 steel, cutting disc, offset type

- Universal disc for complete metal processing
- Hardness: medium
- High cutting output with long tool life
- Uniform in cutting output and tool life
- Maximum working speed 80 m/s

|                             |                       |
|-----------------------------|-----------------------|
| <b>Order no.</b>            | <b>616302000</b>      |
| <b>EAN code</b>             | <b>4007430401090</b>  |
| Quality class               | A 30-R                |
| Diameter x thickness x bore | 230 x 3 x<br>22.23 mm |
| Version                     | offset                |
| Maximum speed               | 6600 rpm              |
| Sales unit / packaging unit | 1 / 25                |