



Flexiamant super 300x2.5x25.4 steel, cutting disc, straight type

- Good cutting output with good tool life in steel
- Hard version for powerful machines (machine load > 3 KW)
- A 36-S: with an inside gauze for quick cuts
- Maximum working speed 80 m/s

Order no.	616328000
EAN code	4007430085726
Quality class	A 30-R
Diameter x thickness x bore	300 x 2.5 x 25.4 mm
Version	straight
Maximum speed	5090 rpm
Sales unit / packaging unit	1 / 10