



Novoflex 115x2.5x22.23 steel, cutting disc, straight type

- Quality Novoflex: powerful entry-level class
- Hardness: medium-hard
- Universal use in metal processing
- Good cutting performance with good tool life.
- Maximum working speed 80 m/s
- Arbeitshöchstgeschwindigkeit 80 m/s

Order no.	616442000
EAN code	4007430122568
Quality class	A 30
Diameter x thickness x bore	115 x 2.5 x 22.23 mm
Version	straight
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25