



## Novoflex 125x2.5x22.23 steel, cutting disc, straight type

- Quality Novoflex: powerful entry-level class
- Hardness: medium-hard
- Universal use in metal processing
- Good cutting performance with good tool life.
- Maximum working speed 80 m/s
- Arbeitshöchstgeschwindigkeit 80 m/s

<b>Order no.</b>	<b>616444000</b>
<b>EAN code</b>	<b>4007430433909</b>
Quality class	A 30
Diameter x thickness x bore	125 x 2.5 x 22.23 mm
Version	straight
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25