



Novoflex 180x3.0x22.23 steel, cutting disc, straight type

- Quality Novoflex: powerful entry-level class
- Hardness: medium-hard
- Universal use in metal processing
- Good cutting performance with good tool life.
- Maximum working speed 80 m/s
- Arbeitshöchstgeschwindigkeit 80 m/s

Order no.	616450000
EAN code	4007430433947
Quality class	A 30
Diameter x thickness x bore	180 x 3 x 22.23 mm
Version	straight
Maximum speed	8500 rpm
Sales unit / packaging unit	1 / 25