



Novoflex 230x6.0x22.23 steel, grinding disc, offset type

- Quality Novoflex: powerful entry-level class
- Hardness: medium-hard
- Universal use in metal processing
- Good cutting output with good tool life
- Maximum working speed 80 m/s

Order no.	616468000
EAN code	4007430088918
Quality class	A 24
Diameter x thickness x bore	230 x 6 x 22.23 mm
Version	offset
Maximum speed	6600 rpm
Sales unit / packaging unit	1 / 10