



## Flexiarapid 125 x 1.0 x 22.23 mm, aluminium, cutting disc, form 41

- Thin high-output cutting disc especially for processing aluminium, non-ferrous metals, copper, brass, bronze etc., thin-walled materials such as pipes, metal sheets, profiles, wires
- Hardness: medium-hard
- High cutting output with long tool life
- Maximum working speed 80 m/s
- Attention: Good extraction is obligatory in closed rooms, as highly concentrated aluminium dust can lead to explosions!

<b>Order no.</b>	<b>616513000</b>
<b>EAN code</b>	<b>4007430248060</b>
Quality class	A 60-P
Diameter x thickness x bore	125 x 1 x 22.23 mm
Version	straight
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25