



Flexiamant super 115x6.0x22.23 stone, grinding disc, offset type

- Special disc for rough grinding on concrete, natural and artificial stone
- Hardness: soft
- High cutting output with good tool life
- Maximum working speed 80 m/s

Order no.	616729000
EAN code	4007430402981
Quality class	C 24-N
Diameter x thickness x bore	115 x 6 x 22.23 mm
Version	offset
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25