



## Flexiamant super 125x6.0x22.23 stone, grinding disc, offset type

- Special disc for rough grinding on concrete, natural and artificial stone
- Hardness: soft
- High cutting output with good tool life
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>616731000</b>
<b>EAN code</b>	<b>4007430403025</b>
Quality class	C 24-N
Diameter x thickness x bore	125 x 6 x 22.23 mm
Version	offset
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25