



## Flexiamant 125x2.5x22.23 steel, cutting disc, straight type

- Universal disc for complete metal processing
- Hardness: medium
- High cutting output with long tool life
- Uniform in cutting output and tool life
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>616732000</b>
<b>EAN code</b>	<b>4007430403032</b>
Quality class	A 30-R
Diameter x thickness x bore	125 x 2,5 x 22,23 mm
Version	straight
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25