



## Flexiamant 125x2.5x22.23 Inox, cutting disc, straight type

- Universal disc for processing stainless steels
- Hardness: soft
- High cutting output with long tool life
- Low in iron and sulphur <0.1%
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>61673800</b>
<b>EAN code</b>	<b>4007430403124</b>
Quality class	A 30-P
Diameter x thickness x bore	125 x 2.5 x 22.23 mm
Version	straight
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25