



Flexiamant super 115x6.0x22.23 Inox, grinding disc, offset type

- Special disc for processing stainless steels
- Low in iron and sulphur <0.1%
- Hardness: soft
- Very good cutting output with good tool life
- Maximum working speed 80 m/s

Order no.	616739000
EAN code	4007430403148
Quality class	A 36-O
Diameter x thickness x bore	115 x 6 x 22.23 mm
Version	offset
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25