



Flexiamant super 125x6.0x22.23 aluminium, grinding disc, offset type

- Special disc with open structure for high cutting output and good tool life
- Hardness: soft
- Best suited for processing lubricating materials such as aluminium, bronze, copper, brass
- Maximum working speed 80 m/s
- Attention: Good extraction is obligatory in closed rooms, as highly concentrated aluminium dust can lead to explosions!

Order no.	61674900
EAN code	4007430403308
Quality class	A 36-M
Diameter x thickness x bore	125 x 6 x 22.23 mm
Version	offset
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25