



Flexiamant 115x2.5x22.23 steel, cutting disc, straight type

- Universal disc for complete metal processing
- Hardness: medium
- High cutting output with long tool life
- Uniform in cutting output and tool life
- Maximum working speed 80 m/s

Order no.	616770000
EAN code	4007430431530
Quality class	A 30-R
Diameter x thickness x bore	115 x 2,5 x 22.23 mm
Version	straight
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25