



Flap disc 178 mm P 40, zirconia alumina "Novoflex"

- Suitable for rough and intermediate grinding in all fields of metalworking including stainless steel, steel, cast iron, and sheet steel
- Quality Novoflex: powerful entry-level class
- Uniform grinding capacity
- Cool grinding
- Uniform grinding result, comfortable grinding with only low vibration
- Most suitable for processing stainless steels
- Maximum working speed 80 m/s
- Tilted version: angle of attack 7-9°

Order no.	623112000
EAN code	4007430087515
Diameter x bore	178 x 22.23 mm // 7 x 7/8 "
Grit	P 40
Version	sloping
Maximum speed	8500 rpm
Sales unit / packaging unit	1 / 10