



Flap disc 115 mm P 40, zirconia alumina "SP"

- Suitable for rough and intermediate grinding in all fields of metalworking including stainless steel, steel, cast iron, and sheet steel
- Uniform grinding capacity
- Cool grinding
- Uniform grinding result, comfortable grinding with only low vibration
- Most suitable for processing stainless steels
- Maximum working speed 80 m/s
- Tilted version: angle of attack 7-9°

Order no.	623144000
EAN code	4061792185807

Diameter x bore	115 x 22.23 mm // 4 1/2 x 7/8 "
-----------------	------------------------------------

Grit	P 40
------	------

Version	sloping
---------	---------

Maximum speed	13300 rpm
---------------	-----------

Sales unit / packaging unit	1 / 10
-----------------------------	--------