



## SDS-max PRO 4 Premium Hammer Drill Bit 14x200x340 mm

- Extremely robust and aggressive full carbide bit head, 4 cutting edges for extraordinary service life and tool life in strong concrete
- Wear marking on both sides of the main plate acts as an indicator allowing you to assess the measure of the dowel holes.
- The 4-spiral helical geometry ensures low-vibration drilling behaviour and low spiral wear
- 90° centering point for precise spot drilling and little breakage at the edge of the drilled hole
- Ideal for use in reinforced concrete and hard natural stone

<b>Order no.</b>	<b>623212000</b>
<b>EAN code</b>	<b>4061792156562</b>
Diameter	14 mm
Working length	200 mm
Overall length	340 mm
Sales unit	1