



SDS-max Pro 4 / 15 x 340 mm

- The slim, chisel-shaped bit head enables fast penetration into the selected material.
- Short spiral inlets and large boring dust grooves in the optimised double delivery helix ensure quick boring dust discharge.
- The continuous core reinforcement ensures stability and durability. It enables maximum energy transmission from rotary hammer to drill tip.
- For use in concrete, masonry, natural stone

Order no.	623315000
EAN code	4007430438072
Diameter	15 mm
Working length	200 mm
Overall length	340 mm
Sales unit	1