



SDS-max Pro 4 / 18 x 540 mm

- Unrivalled destructive force: Extremely robust and aggressive solid carbide S-blade
- Constant high lifetime: Short head with large-volume dust channels for smooth transport of the drill dust, minimum generation of heat
- Highest drilling speed: Inclined auxiliary cutting edges for aggressive drill progress
- Optimum centring: Drill-active centering point for optimum guidance when drilling in concrete and armoured concrete
- Precise drilling hole diameters: innovative wear indication (indicator for dimensional conformance)
- Vibration Control: optimised vibration values - ideal for the hardest applications on the construction site
- For use in concrete, masonry, natural stone

| | |
|------------------|----------------------|
| Order no. | 623320000 |
| EAN code | 4007430437792 |

| | |
|----------------|--------|
| Diameter | 18 mm |
| Working length | 400 mm |
| Overall length | 540 mm |
| Sales unit | 1 |