



## SDS-max PRO 4 Premium hammer drill bit 24x400x520 mm

- Unrivalled destructive force: Extremely robust and aggressive solid carbide S-blade
- Constant high lifetime: Short head with large-volume dust channels for smooth transport of the drill dust, minimum generation of heat
- Highest drilling speed: Inclined auxiliary cutting edges for aggressive drill progress
- Optimum centring: Drill-active centering point for optimum guidance when drilling in concrete and armoured concrete
- Precise drilling hole diameters: innovative wear indication (indicator for dimensional conformance)
- Vibration Control: optimised vibration values - ideal for the hardest applications on the construction site
- For use in concrete, masonry, natural stone

<b>Order no.</b>	<b>623328000</b>
<b>EAN code</b>	<b>4007430437877</b>

Diameter	24 mm
Working length	400 mm
Overall length	520 mm
Sales unit	1