



Cup brush 80x0.5 mm/ M 14, steel-wire, twisted, wire thickness 0.50 mm

- For universal use in metal processing, e.g. for cleaning, deburring, purging, removing rust, smoothing welding seams and points, stripping slag, scales and old paint
- For processing large areas, weld seams etc.
- Edging type: twisted steel wire

Order no.	623710000
EAN code	4007430407757
Diameter	80 mm / 3.15 "
Female thread	M 14
Wire thickness	0.50 mm
Maximum speed	8600 rpm
Sales unit / packaging unit	1 / 1