



**Cup brush 100x0.5 mm/ M 14, steel-wire,  
twisted, wire thickness 0.50 mm**

- For universal use in metal processing, e.g. for cleaning, deburring, purging, removing rust, smoothing welding seams and points, stripping slag, scales and old paint
- For processing large areas, weld seams etc.
- Edging type: twisted steel wire

<b>Order no.</b>	<b>623711000</b>
<b>EAN code</b>	<b>4007430407764</b>
Diameter	100 mm / 4 "
Female thread	M 14
Wire thickness	0.50 mm
Maximum speed	8600 rpm
Sales unit / packaging unit	1 / 1