



**Cup brush 100x0.3 mm/ M 14, steel-wire,
crimped, wire thickness 0.30 mm**

- For light surface processing and deburring work in all metal processing
- For processing larger areas, weld seams, metal plates
- Edging type: crimped steel wire

| | |
|-----------------------------|---------------|
| Order no. | 623719000 |
| EAN code | 4007430407849 |
| Diameter | 100 mm |
| Female thread | M 14 |
| Wire thickness | 0.30 mm |
| Maximum speed | 8600 rpm |
| Sales unit / packaging unit | 1 / 1 |